

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: DM/44**

**Order data**

Order number	264838 DM/44
GTIN	4251414902985
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: DVUNR

suitable indexable insert: VN.. 1604..

Approach angle: 93 °

Minimum pre-drill  $\varnothing D_{\min}$ : 50 mm

Centre offset  $L_3$ : 29 mm

**Technical description**

Series	Master Mute
Cutting point / joint	40 mm

ISO code cutting head	DVUNR
System	DM
suitable indexable insert	VN.. 1604..
Shim screw	259027 3
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Approach angle	93 °
Clamp, screw, O-ring	259036 7
Shim	259033 5
Overall length L	35 mm
Centre offset L <sub>3</sub>	29 mm
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX10	674248 TX10
Shim Type 5	259033 5
Shim screw Type 4	259027 4
Shim	259227
Shim screw Type 3	259027 3
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamp unit	259509
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim	259228
Clamp unit Type 5	259036 5
Shim screw	259613
Shim screw	259614

Shim Type 6	259033 6
Clamp unit	259507
Clamp unit Type 7	259036 7