

Garant**GARANT Master Mute cutting head, left-hand, System / insert size: DM/44****Order data**

Order number	264839 DM/44
GTIN	4251414902992
Item class	29D

Description**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: DVUNL

suitable indexable insert: VN.. 1604..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 50 mm

Centre offset L_3 : 29 mm

Technical description

Cutting point / joint	40 mm
Minimum pre-drill $\varnothing D_{\min}$	50 mm

suitable indexable insert	VN.. 1604..
Series	Master Mute
Clamp, screw, O-ring	259036 18
Shim	259033 5
Centre offset L ₃	29 mm
Shim screw	259027 3
System	DM
Overall length L	35 mm
ISO code cutting head	DVUNL
Approach angle	93 °
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Shim screw	259613
Clamp unit Type 18	259036 18
Shim Type 5	259033 5
Shim screw Type 3	259027 3
Clamp unit Type 7	259036 7
Shim	259227
Clamp unit	259509
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500