

**Garant**
**GARANT Master Mute cutting head, left-hand, System / insert size: DM/49**

**Order data**

Order number	264839 DM/49
GTIN	4251414902756
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: STUCL

suitable indexable insert: TC.. 16T3..

Approach angle: 93 °

Minimum pre-drill  $\varnothing D_{\min}$ : 49 mm

Centre offset  $L_3$ : 27 mm

**Technical description**

ISO code cutting head	STUCL
Centre offset $L_3$	27 mm

System	DM
Overall length L	32 mm
Series	Master Mute
suitable indexable insert	TC.. 16T3..
Approach angle	93 °
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Insert screw	269023 3
Shim screw	269015 2
Shim	259033 4
Cutting point / joint	40 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

## Accessories

Clamping screw	269433
Insert screw Type 3	269023 3
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500