

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: DM/50

Order data

Order number	264839 DM/50
GTIN	4251414902961
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: SVUCL

suitable indexable insert: VC.. 1604..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 49 mm

Centre offset L_3 : 27 mm

Technical description

Cutting point / joint	40 mm
Shim screw	269015 2

Centre offset L ₃	27 mm
System	DM
suitable indexable insert	VC.. 1604..
Minimum pre-drill Ø D _{min}	49 mm
Shim	259033 5
Series	Master Mute
Insert screw	269023 3
Approach angle	93 °
ISO code cutting head	SVUCL
Overall length L	32 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Insert screw Type 1	269023 1
Clamping screw	269433
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Insert screw Type 3	269023 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500