

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: ST/16**

**Order data**

Order number	264826 ST/16
GTIN	2050002059269
Item class	29D

**Description**
**Suitable for :**

Boring bar shanks No. 320102; 320103; 320407 and 320408.

Through-coolant: yes

Cutting point / joint: 32 mm

ISO code indexable cutting head: SVQBR

suitable indexable insert: VB.. 1604..

Approach angle: 107.5 °

Minimum pre-drill  $\varnothing D_{\min}$ : 40 mm

Centre offset  $L_3$ : 22 mm

**Technical description**

Insert screw	320626 S05/07
Centre offset $L_3$	22 mm
Minimum pre-drill $\varnothing D_{\min}$	40 mm
ISO code cutting head	SVQBR

Insert assignment	left-hand and neutral
Overall length L	35 mm
suitable indexable insert	VB.. 1604..
Insert size	16 mm
Cutting point / joint	32 mm
Approach angle	107.5 °
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

---

## Accessories

Torx-screw No. 2 Type 2	320626 2
-------------------------	----------