

**Garant**
**Jobber drill extra long HSS N, uncoated, Ø DC h8 × overall length L:  
11,5X365mm**

**Order data**

Order number	116245 11,5X365
GTIN	4062406264857
Item class	11B

**Description**
**Version:**

With precision ground point.

Vaporised high performance drills for drilling particularly deep holes. Take particular care to ensure **frequent chip clearance**.

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

**Note:**

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability

**Technical description**

recommended maximum drilling depth $L_2$	232.8 mm
Tolerance nominal Ø	h8
Standard	DIN 1869
Shank Ø $D_s$	11.5 mm
Nominal Ø $D_c$	11.5 mm
Number of cutting edges Z	2
Overall length L	365 mm
Feed f in steel < 750 N/mm <sup>2</sup>	0.1 mm/rev.
Point angle	118 degrees

Flute length $L_c$	250 mm
Shank	Plain shank
Coating	uncoated
Tool material	HSS
Type	N
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	50 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	32 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	28 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	21 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	18 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	5 m/min	P
GG(G)	suitable	18 m/min	K
Oil	suitable		
wet maximum	suitable		