

**Cleaner Ball, Ball Ø / type: 60H****Order data**

Order number	358971 60H
GTIN	4020772017583
Item class	38L

**Description****Version:**

Suitable for collets or Weldon arbors (clamping Ø 16 mm). Mounting in the headstock of CNC machines. For automatic cleaning. Horizontal version.

**Advantage:**

- **Thorough cleaning of the machine room.**
- **Reduction of the cleaning time.**
- **Working area of 360°.**

**Function:**

Optimum cleaning of the inside of a CNC machine is achieved by rotation of the ball and movement of the spindle. The cleaning medium is the cooling lubricant that is fed through the spindle.

**Technical description**

Pressure	5 - 120 bar
Speed	100 min <sup>-1</sup>
Shank Ø	16 mm
Version	horizontal

Length L	120 mm
Number of outlets	15 pcs.
Type of product	Cleaning ball