

Garant

Jobber drill, extra long HSS-E FS, uncoated, Ø DC h8 × overall length L: 10X430mm



Order data

| | |
|--------------|---------------|
| Order number | 116250 10X430 |
| GTIN | 4062406266097 |
| Item class | 11B |

Description

Version:

With precision ground point.

Special 4-chamfer relief ground for very good guidance within the bore. Bright finish flutes, nitrided chamfers.

With point geometry shape C.

Advantage:

Special deep hole drills. For particularly deep or recessed holes. Good chip evacuation due to parabolic flutes, resulting in fewer chip evacuations even in particularly deep holes.

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

Technical description

| | |
|---|-------------|
| Flute length L_c | 295 mm |
| Feed f in steel < 750 N/mm ² | 0.1 mm/rev. |
| Shank Ø D_s | 10 mm |
| Number of cutting edges Z | 2 |
| Overall length L | 430 mm |
| Standard | DIN 1869 |

| | |
|--|--------------|
| Nominal $\varnothing D_c$ | 10 mm |
| Tolerance nominal \varnothing | h8 |
| Point angle | 130 degrees |
| recommended maximum drilling depth L_2 | 280 mm |
| Shank | Plain shank |
| Coating | uncoated |
| Tool material | HSS E |
| Type | FS |
| Helix angle | 38 degrees |
| Through-coolant | no |
| Colour ring | without |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------|----------|
| Alu plastics | suitable only under restricted conditions | 55 m/min | N |
| Aluminium (short chipping) | suitable only under restricted conditions | 30 m/min | N |
| Steel < 500 N/mm ² | suitable | 32 m/min | P |
| Steel < 750 N/mm ² | suitable | 25 m/min | P |
| Steel < 900 N/mm ² | suitable | 20 m/min | P |
| Steel < 1100 N/mm ² | suitable | 5 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 8 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 4 m/min | M |
| GG(G) | suitable only under restricted conditions | 20 m/min | K |
| Oil | suitable | | |

wet maximum

suitable