

Garant

Jobber drill, extra long HSS-E FS, uncoated, Ø DC h8 × overall length L: 9X250mm



Order data

Order number	116250 9X250
GTIN	4062406266042
Item class	11B

Description

Version:

With precision ground point.

Special 4-chamfer relief ground for very good guidance within the bore. Bright finish flutes, nitrided chamfers.

With point geometry shape C.

Advantage:

Special deep hole drills. For particularly deep or recessed holes. Good chip evacuation due to parabolic flutes, resulting in fewer chip evacuations even in particularly deep holes.

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

Technical description

Flute length L_c	175 mm
Overall length L	250 mm
Point angle	130 degrees
Standard	DIN 1869
Nominal Ø D_c	9 mm
Tolerance nominal Ø	h8

Shank $\varnothing D_s$	9 mm
Feed f in steel $< 750 \text{ N/mm}^2$	0.1 mm/rev.
recommended maximum drilling depth L_2	161.5 mm
Number of cutting edges Z	2
Shank	Plain shank
Coating	uncoated
Tool material	HSS E
Type	FS
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	55 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	30 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	32 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	25 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	20 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	5 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable only under restricted conditions	8 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable only under restricted conditions	4 m/min	M
GG(G)	suitable only under restricted conditions	20 m/min	K
Oil	suitable		

wet maximum

suitable