

**Cleaner Ball, Ball Ø / type: 60V****Order data**

Order number	358971 60V
GTIN	4020772017590
Item class	38L

**Description****Version:**

Suitable for collets or Weldon arbors (clamping Ø 16 mm). Mounting in the headstock of CNC machines. For automatic cleaning. Vertical version.

**Advantage:**

- **Thorough cleaning of the machine room.**
- **Reduction of the cleaning time.**
- **Working area of 360°.**

**Function:**

Optimum cleaning of the inside of a CNC machine is achieved by rotation of the ball and movement of the spindle. The cleaning medium is the cooling lubricant that is fed through the spindle.

**Technical description**

Speed	100 min <sup>-1</sup>
Version	vertical
Length L	110 mm
Shank Ø	16 mm
Number of outlets	14 pcs.

Pressure	5 - 120 bar
Type of product	Cleaning ball