

**Garant****GARANT Master Tap machine tap HSS-E-PM 6HX, AlTiX, MF: 7X0,5****Order data**

Order number	132905 7X0,5
GTIN	4062406265625
Item class	11I

**Description****Version:**

**GARANT Master Tap Universal taps**, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

**Technical description**

Number of clamping slots	3
Thread pitch	0.5 mm
Tapping hole Ø	6.5 mm
Shank Ø D <sub>s</sub>	5.5 mm
Shank square □	4.3 mm
Tool material	HSS E PM
Number of cutting edges Z	3
Thread Ø	7 mm
Tolerance class	ISO 2X 6HX
Overall length L	80 mm
Standard	DIN 374
Thread depth	21 mm

Thread type	MF
Thread size	M7×0.5
Coating	AlTiX
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	8 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	10 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K

CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		