



Pneumatic screwdriver, Type: S2370



Order data

Order number	079163 S2370
GTIN	7322590011420
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.

- **With slip clutch.**
- **Adjustable torque setting.**
- **Reversible for clockwise/ anticlockwise rotation.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674205 ff).

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

maximum screw Ø (8.8 - 12.9)	M5
Manufacturer's designation	S2370
Operating noise	83 dB(A)
recommended hose size (internal Ø)	6.3 mm
Weight	0.9 kg
maximum speed	1300 min ⁻¹
Format	Rod

Torque range	2 – 6 Nm
maximum air consumption	240 l/min
maximum vibration to EN	< 2.5 m/s ²
Compressed air connection	1/4 in
Connection thread	BSP
Bit socket	F 6.3
Power supply	Pneumatic
Type of product	Screwdriver