

Garant
GARANT Master Steel DEEP solid carbide deep hole drill, plain shank DIN 6535 HA 25×D, TiAlN, Ø DC j6: 3,3mm

Order data

Order number	123893 3,3
GTIN	4062406268381
Item class	10E

Description
Version:

Excellent chip evacuation due to the unequal helical pitch of the flutes, guide rings and additional flute lands for very high precision when drilling. **Maximum process reliability** due to exactly matching tools within the overall system. Drilling up to the maximum depth without a pilot drill. **Significantly increased tool stability** due to the substantially strengthened core. **Increased metal removal rates** and **outstanding tool lives** lead to an economical high-end drilling process.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$. For deep holes greater than $20 \times D$, a pilot hole to the maximum drilling depth with pilot drill No. 123885 is absolutely essential. The generation of a pilot hole improves process reliability. **The specified L/D ratio gives the minimum achievable depth of hole with the respective deep-hole drill.**

Technical description

Number of cutting edges Z	2
Feed f in steel < 900 N/mm ²	0.09 mm/rev.
Standard	Manufacturer's standard
Nominal Ø D _c	3.3 mm
Tolerance nominal Ø	j6
Flute length L _c	97 mm
recommended maximum drilling depth L ₂	92.05 mm
Shank Ø D _s	6 mm

Overall length L	140 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Version	25×D
Point angle	138 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 40 bar
Machining strategy	HPC
Pilot drill required	yes, pilot drill
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	110 m/min	P
Steel < 750 N/mm ²	suitable	100 m/min	P
Steel < 900 N/mm ²	suitable	95 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	95 m/min	P
Steel < 1400 N/mm ²	suitable	75 m/min	P
INOX < 900 N/mm ²	suitable	60 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	55 m/min	M
GG(G)	suitable	100 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

