



Digital length measurement probe set μ Finder GT, Type: 31



Order data

Order number	434718 31
GTIN	7630041143669
Item class	45A

Description

Version:

Mobile high-precision set for parallelism and straightness measurements, and for alignment of machines in quality control and service.

Sturdy portable display unit with scale and digital display for inductive measurement probes.

Clear and error-free reading thanks to the highly detailed scale display. 5 \times zoom mode. Very long running time of more than 300 hours. Optimum handling due to ergonomic design and soft touch surface.

- **Adjustable-angle measuring tip for measurements in two directions.**
- **Ball-bearing lifting system with mass balancing.**
- **Collision-protection by means of two slip clutches.**
- **Contact point with \varnothing 2 mm carbide ball - can pivot through 180°.**
- **Independent change of sensing direction, without change of arithmetic sign.**
- **Case with two dovetail bars.**

Supplied with:

Supplied with instruction handbook, portable TWIN-T10 display unit No. 434716 size T10, 4 \times batteries No. 081561 size LR6, small magnetic stand, case. Including lever contact point No. 434779 size GT31.

Technical description

Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 LR6
Gauging force	0.2 N
Clamping shank Ø h6	8 mm
Span of measurement	0.3 mm
Power supply	Battery-powered
Reversible reading	mm / inch
Interface	TESA Link Connector TLC
Interface	Digimatic interface
Interface	Digimatic interface
Measurement technology	digital
Type of product	Lever dial indicator