

## Garant

### GARANT Master Steel solid carbide mini milling cutter HPC, TiAlN, Ø e8 DC: 1,5mm



#### Order data

Order number	202289 1,5
GTIN	4062406271107
Item class	11X

#### Description

##### Version:

**Extra short cutter** for maximum stability. **Shank length to DIN** for improved support of the tool in the holder. This significantly increases the tool life.

**Save the regrinding costs:** It is cheaper to use a carbide mini slot drill to the limit of wear and throw it away, than to regrind it.

Tool for **general-purpose machining**.

##### Note:

HB shanks are available at the same price as HA.

For **HB** shanks use order **no. 202291**.

#### Technical description

Cutting edge Ø D <sub>c</sub>	1.5 mm
Tolerance nominal Ø	e8
Flute length L <sub>c</sub>	3 mm
Direction of infeed	horizontal, oblique and vertical
No. of teeth Z	3
Feed f <sub>z</sub> for slot milling in steel < 900 N/mm <sup>2</sup>	0.005 mm
Helix angle	30 degrees
Shank	DIN 6535 HA to h6
Shank Ø D <sub>s</sub>	3 mm

Overall length L	38 mm
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.006 mm
Corner chamfer angle	90 degrees
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	290 m/min	N
Alu > 10% Si	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	50 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	70 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	40 m/min	S

GG(G)	suitable	85 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		