



Permanent magnetic circular chuck, with radial pole distribution, Chuck Ø: 500mm



Order data

Order number	380810 500
GTIN	2050002040304
Item class	33S

Description

Version:

- Neodymium magnet system for strong clamping force.
- Concentric grooves to assist component alignment.
- Centre is magnetically inactive, so that the plate can be bored through.

ON-OFF control by hand-operated lever.

Application:

- For grinding and turning.
- Particularly suitable for clamping annular components, due to radial pole distribution.
- For round and annular workpieces

Technical description

Nominal clamping force	150 N/cm ²
Centre Ø	200 mm
maximum boring-out Ø	58 mm
Thread Ø	8×M8

Pitch circle Ø	360 / 440 mm
Chuck Ø	500 mm
Centring hole depth	8 mm
Ø non-magnetic core	60 mm
Weight	144 kg
Height	92 mm
Height tolerance	+0.5 / -2 mm
Type of product	Magnetic clamping chuck