

**Wet and dry vacuum cleaner AERO, Manufacturer's designation: 21-21INOX****Order data**

Order number	078540 21-21INOX
GTIN	5711145158864
Item class	07C

Description**Version:**

Robust and powerful **wet / dry vacuum cleaners** with flexible hose connection system (MultiFit) and for performing a very wide variety of professional cleaning tasks. **Degree of separation > 99.9%**. Compact all-purpose vacuum cleaner with Push & Clean **filter cleaning system**.

- **With socket and automatic switch-on for connection of an electric power tool (maximum 2000 W).**
- **Stainless steel tank with handle and hose clip.**

Supplied with:

Supplied with suction hose, hose support, curved hand tube, wet filter and washable filter element (PET).

Note:

Other safety vacuum cleaners for all hazard classes (health hazard or explosive dusts) are available on request (class L, M, H).

Technical description

Container volume	20 l
Manufacturer's designation	AERO 21-21 PC INOX

Automatic switch-on	yes
Filter cleaning	Push & Clean system
Width	400 mm
Length	390 mm
Weight	8.5 kg
Number of turbines	1
Height	525 mm
Suction hose length	2.5 m
Operating noise	64 dB(A)
Cable length	5 m
Power consumption	1250 W
Degree of separation	99.9 %
Air flow volume	60 l/s
Vacuum	210 mbar
Hose Ø	32 mm
Special features	Compact stainless steel container
Filter system	PET filter element
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

Accessories

Floor nozzle, 400 mm wide Manufacturer's designation
3666

078555 3666

Stainless steel extension tube Manufacturer's designation
8074

078556 8074