


Garant
GARANT Master Steel solid carbide mini-milling cutter HPC, TiAlN, Ø e8 DC: 3,5mm

Order data

Order number	202297 3,5
GTIN	4062406271886
Item class	11X

Description
Version:

Extra short cutter for maximum stability. **Shank length to DIN** for improved support of the tool in the holder. This significantly increases the tool life.

Save the regrinding costs: It is cheaper to use a carbide mini slot drill to the limit of wear and throw it away, than to regrind it.

Tool for **general-purpose machining**.

Technical description

Flute length L_c	6 mm
Shank $\varnothing D_s$	6 mm
Feed f_z for slot milling in steel $< 900 \text{ N/mm}^2$	0.02 mm
Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.022 mm
Direction of infeed	horizontal, oblique and vertical
No. of teeth Z	3
Shank	DIN 6535 HB to h6
Cutting edge $\varnothing D_c$	3.5 mm
Helix angle	45 degrees
Corner chamfer width at 45°	0.03 mm
Tolerance nominal \varnothing	e8

Overall length L	50 mm
Corner chamfer angle	45 degrees
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	290 m/min	N
Alu > 10% Si	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	140 m/min	P
Steel < 750 N/mm ²	suitable	120 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	50 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG(G)	suitable	85 m/min	K

Uni	suitable
wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable