

## Garant

### GARANT Master Steel DEEP solid carbide deep hole drill, plain shank DIN 6535 HA 20×D, TiAlN, Ø DC: 5mm



#### Order data

Order number	123890 5
GTIN	4062406268091
Item class	10E

#### Description

##### Version:

**Excellent chip evacuation** due to the unequal helical pitch of the flutes, guide rings and additional guide chamfers for very high precision when drilling. **Maximum process reliability** due to exactly matching tools within the overall system. Drilling up to the maximum depth without a pilot drill. **Significantly increased tool stability** due to the substantially strengthened core. **Increased metal removal rates** and **outstanding tool lives** lead to an economical high-end drilling process.

##### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

For process reliability when using the 16×D deep-hole drill, initial centre drilling with No. 121068 – 121121 or a pilot hole of at least 4×D with pilot drill No. 122736 is necessary. For deep holes greater than 20×D, a pilot hole to the maximum drilling depth with pilot drill No. 122736 is absolutely essential. The generation of a pilot hole improves process reliability. **The specified L/D ratio gives the minimum achievable depth of hole with the respective deep-hole drill.**

#### Technical description

Number of cutting edges Z	2
Standard	Manufacturer's standard
Overall length L	155 mm
Tolerance nominal Ø	j6
recommended maximum drilling depth $L_2$	105.5 mm
Nominal Ø $D_c$	5 mm

Flute length $L_c$	113 mm
Feed $f$ in steel $< 900 \text{ N/mm}^2$	0.11 mm/rev.
Shank $\varnothing D_s$	6 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Version	20xD
Point angle	138 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 40 bar
Machining strategy	HPC
Pilot drill required	yes, pilot drill
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable	120 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	110 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	105 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	105 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	85 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable	65 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable only under restricted conditions	60 m/min	M
Ti $> 850 \text{ N/mm}^2$	suitable only under restricted conditions	25 m/min	S
GG(G)	suitable	110 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions