



Flap wheel (A), 150 grit, Head \varnothing ×head width: 15X30mm



Order data

Order number	555035 15X30
GTIN	4027497608850
Item class	56L

Description

Version:

Flap strips bonded on to the shank of the tool. Inserted strips bonded at the end.

Application:

Deburring of holes, cross holes and pipe internal diameters. The abrasive strips adapt to the diameter of the component. Radial use.

Technical description

Shank \varnothing	6 mm
maximum speed	18000 min ⁻¹
Overall length	100 mm
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	150 grit
Type of product	Flap wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		

Steel < 1400 N/mm ²	suitable only under restricted conditions
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable only under restricted conditions
GG(G)	suitable only under restricted conditions
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable
dry	suitable