



Flap wheel (A), 150 grit, Head Ø×head width: 20X10mm



Order data

| | |
|--------------|---------------|
| Order number | 555035 20X10 |
| GTIN | 4027497608874 |
| Item class | 56L |

Description

Version:

Flap strips bonded on to the shank of the tool. Inserted strips bonded at the end.

Application:

Deburring of holes, cross holes and pipe internal diameters. The abrasive strips adapt to the diameter of the component. Radial use.

Technical description

| | |
|------------------------|--------------------------|
| Shank Ø | 6 mm |
| maximum speed | 18000 min ⁻¹ |
| Overall length | 100 mm |
| Grinding media | Aluminium Oxide grit (A) |
| Grinding medium code | A |
| Product name attribute | 150 grit |
| Type of product | Flap wheel |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|-------------|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |

| | |
|--------------------------------|---|
| Steel < 1400 N/mm ² | suitable only under restricted conditions |
| Steel < 55 HRC | suitable |
| Steel < 60 HRC | suitable only under restricted conditions |
| GG(G) | suitable only under restricted conditions |
| CuZn | suitable |
| Plastic, GRP | suitable |
| Wood | suitable |
| dry | suitable |