

Pneumatic-hydraulic pop rivet tool, Type: RAC211



Order data

Order number	770513 RAC211
GTIN	8033371217304
Item class	72E

Description

Version:

Operating pressure 6 – 7 bar. Removable rivet pin capture box. Powerful and reliable pop riveter. Quick and reliable securing of pop rivets due to the powerful gripping system (grips the rivet pin without slipping). Variably adjustable suction to dispose the snapped rivet pins into the capture box.

Supplied with:

Nozzles (suitable for steel, stainless steel, aluminium, copper): 2.4; 2.4-3.4 and 4 mm. Nozzle (suitable for aluminium): 4.8 mm. 1 bottle hydraulic oil 50 ml.

Technical description

for pop rivets in all materials up to	4 mm
for pop rivets aluminium up to	4.8 mm
Weight	1.4 kg
Air consumption per rivet	3.4 l
Tool stroke	16 mm
maximum mandrel Ø	2.5 mm

Hose connection	8 mm
Setting force at 6 bar	6600 N
Operating pressure	6 - 7 bar
Type of product	Pop riveter