

Garant

GARANT Master Steel solid carbide mini milling cutter HPC, TiAlN, Ø e8 DC: 12mm



Order data

Order number	202295 12
GTIN	4062406271497
Item class	11X

Description

Version:

Extra short cutter for maximum stability. **Shank length to DIN** for improved support of the tool in the holder. This significantly increases the tool life.

Save the regrinding costs: It is cheaper to use a carbide mini slot drill to the limit of wear and throw it away, than to regrind it.

Tool for **general-purpose machining**.

Note:

HB shanks are available at the same price as HA.

For **HB shanks** use order **no. 202297**.

Technical description

Helix angle	45 degrees
Overall length L	73 mm
Shank	DIN 6535 HA to h6
Cutting edge Ø D _c	12 mm
Flute length L _c	16 mm
Feed f _z for side milling in steel < 900 N/mm ²	0.07 mm
Tolerance nominal Ø	e8
No. of teeth Z	3
Feed f _z for slot milling in steel < 900 N/mm ²	0.06 mm

Shank $\varnothing D_s$	12 mm
Direction of infeed	horizontal, oblique and vertical
Corner chamfer width at 45°	0.05 mm
Corner chamfer angle	45 degrees
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width a_e for milling operation	Full slot cutting depth 1xD
Cutting width a_e for milling operation	Full slot cutting depth 1xD
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	290 m/min	N
Alu > 10% Si	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	140 m/min	P
Steel < 750 N/mm ²	suitable	120 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	50 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M

Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG(G)	suitable	85 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		