

**Garant****Abrasive cap (SiC), 150 grit, Abrasive cap Ø, -length, shape: 1319C****Order data**

Order number	553328 1319C
GTIN	4062406272074
Item class	51E

**Description****Version:**

**Silicon carbide (SiC)** ideal for grinding titanium, aluminium and alloys of those metals.

**Application:**

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

**Note:**

Compatible only for use with ground abrasive cap holder No. 553100.

**Technical description**

Abrasive cap Ø	13 mm
recommended speed	16000 min <sup>-1</sup>
Shape	C
Abrasive cap length	19 mm
Grinding media	Silicon carbide (SiC)

Grinding medium code	SiC
Grit	150
Product name attribute	150 grit
Type of product	Abrasive cap

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Carbide (HM)	suitable		
Ti	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
dry	suitable		

## Accessories

Abrasive cap holder Head Ø, head length, shape 1319C	553100 1319C
--	--------------