

Garant**Pair of gloves MASTER CUT B OIL, Glove size: 11****Order data**

Order number	094417 11
GTIN	4062406273569
Item class	01H

Description**Version:**

Close-fitting and extremely comfortable thanks to 18-gauge knitting technology. Pleasant nitrile micro-foam coating for exceptionally good sense of touch and high degree of dexterity. Therefore highly suitable for precise handling of sharp-edged parts. Also ideal for wet or oily environments thanks to 3/4 nitrile coating that extends over the knuckles. A second coating layer of sanded nitrile on the palm of the hand and fingers ensures a particularly secure grip. With reinforced thumb joint for longer working life.

GARANT MASTER CUT B OIL. Very flexible cut-resistant gloves with cut protection level B. Highly suitable for **oily working environments with moderate cut hazards**, e.g. on cutting machines.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	11
------------	----

Series	MASTER CUT
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	DMF-free
Knitted technology	18G
Clothing standard	Oeko-Tex Standard 100
EN 388	4X42B
Backing material	HPPE
Coating	Nitrile
Coating variant	3/4 coating
Application range	All-round
Application range	Precision
Colour	grey / black
Length	250 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves