



Pneumatic-hydraulic pop rivet tool, Type: RAC181



Order data

Order number	770513 RAC181
GTIN	8033371209507
Item class	72E

Description

Version:

Operating pressure 6 – 7 bar. Removable rivet pin capture box. Powerful and reliable pop riveter. Quick and reliable securing of pop rivets due to the powerful gripping system (grips the rivet pin without slipping). Variably adjustable suction to dispose the snapped rivet pins into the capture box.

Supplied with:

Supplied with nozzles (suitable for steel, stainless steel, aluminium, copper): 2.4; 2.4-3.4 and 4.8 mm.

Nozzle (suitable aluminium): 6-6.4 mm.

1 bottle hydraulic oil 50 ml.

Tool stroke: 21 mm

Setting force at 6 bar: 10500 N

Air consumption per rivet: 5.4 l

Hose connection: 8 mm

maximum mandrel Ø: 3.2 mm

for pop rivets in all materials up to: 4.8 mm

Technical description

Air consumption per rivet	5.4 l
Tool stroke	21 mm
for pop rivets aluminium up to	6.4 mm
maximum mandrel Ø	3.2 mm
for pop rivets in all materials up to	4.8 mm
Setting force at 6 bar	10500 N
Weight	1.6 kg
Hose connection	8 mm
Operating pressure	6 - 7 bar
Type of product	Pop riveter