


Garant**CNMG 160616, Grade: HB725**

Order data

Order number	250172 HB725
GTIN	4062406272234
Item class	21G

Description

CNMG 160616 HB725 Grade: HB725
Chip breaker: UM
Tolerance: M
Cutting depth a_p : 0.2 - 6 mm
Feed f : 0.05 - 0.6 mm/rev.
Cutting speed v_c main application: 50 - 250 m/min

Technical description

Cutting depth a_p	0.2 - 6 mm
Number of changes/inserts	4
Cutting speed v_c main application	50 - 250 m/min
Feed f	0.05 - 0.6 mm/rev.
Tool material	Carbide
ISO code indexable insert	CNMG 120412
Corner radius	1.2 mm

Main application	UNI
Finishing/roughing assignment	Semi-roughing
Coating	TiCN
Grade	HB725
Cutting conditions	slightly interrupted
Chip breaker	UM
Tolerance	M
Type of product	Indexable insert for turning