

Honeywell**Pair of gloves CoreShield™ 22-7518B, Glove size: 10****Order data**

| | |
|--------------|-----------|
| Order number | 094520 10 |
| GTIN | |
| Item class | 09A |

Description**Version:**

Honeywell CoreShield™ series. The innovative light-weight cut-resistant gloves series offers **very good touch sensitivity** and pleasant freedom of movement for the fingers. In addition the series scores well for long shelf life and high sturdiness. The resilient and **breathable micro-foam coating** ensures excellent non-slip characteristics for the gloves on both oily and dry surfaces.

CoreShield™ 22-7518B. Cut-resistant gloves with cut protection level B and **18-gauge knitted technology** for precision work with medium cut hazards. High wearing comfort, thanks to the **HPPE** backing material.

Standard:

EN 388; EN 420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. The **CoreShield™ series** is available in various knitted thicknesses (10 to **18 gauge**) and coatings (nitrile micro-foam, super thin nitrile).

Technical description

| | |
|----------------------------|---------------------|
| Manufacturer's designation | CoreShield 22-7518B |
|----------------------------|---------------------|

| | |
|-----------------------|--------------------------------|
| Contents | 10 |
| Glove characteristics | Suitable for touch screens |
| Glove characteristics | Suitable for allergy sufferers |
| Glove characteristics | Reinforced crook of the thumb |
| Glove characteristics | Silicone-free |
| Glove characteristics | DMF-free |
| Knitted technology | 18G |
| Clothing standard | Oeko-Tex Standard 100 |
| EN 388 | 4X31B |
| Backing material | HPPE |
| Coating | Nitrile micro-foam |
| Coating variant | The palms of the hands |
| Application range | Precision |
| Colour | grey / black |
| Weight | 35-55 g |
| Length | 220 - 270 mm |
| Application | reusable |
| Cut protection class | B |
| Type of product | Cut-resistant gloves |