



“BIG Twin Move” tool case, Type: 1



Order data

Order number	692615 1
GTIN	4003773071549
Item class	64D

Description

Version:

Hard-wearing version of ABS material in black with all-round aluminium frame and metal hinges. The case comes with a sturdy and ergonomic carrying handle. 2 stickers for individual identification are supplied for the labelling field. The tool boards consist of dirt-repellent PP twin-wall sheets.

With a telescopic handle recessed into the base, and two free-running skater rollers on the outer edges for comfortable transport.

Free standing in all opening positions, thanks to stepped cover struts on each side with hinge mechanisms; the angle can be freely selected. Can be opened from one side or both sides. Base and cover can be opened independently of each other, and each has 2 metal rocker switches for fixing the position. In addition the base can be secured by 1 three-digit combination switch.

Internal equipment:

a total of 95 insertion points:

Cover:

1 tool board with 12 insertion pockets and 1 flat pocket on the front face and 10 elastic straps on the back face.

1 tool board with 7 elastic straps and 1 clamping pocket in the cover.

Centre part with 37 elastic straps.

Base:

1 base tray (secured with a push stud) with 3 longitudinal dividers (3× long)
1 tool board with 12 insertion pockets and 1 flat pocket as a cover for the base tray.
Centre part with 15 elastic straps and 13 insertion pockets.

Technical description

Internal dimension length	490 mm
Internal dimension height	210 mm
Weight	8.6 kg
Internal dimension width	370 mm
Manufacturer's designation	BIG Twin Move
Material	ABS
Type of tool storage	Shaft pockets
Case load capacity	30 kg
wheeled	yes
Type of product	Tool transport system