



LED cordless work lamp, Type: 16



Order data

Order number	081254 16
GTIN	5708997354568
Item class	08C

Description

Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

NOVA work lamps with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB charging cable and plug-in power supply unit.

Technical description

Type of rechargeable battery	Lithium-ion
IP Index of Protection	IP 67
CRI value	80
Battery voltage	3.7 V

Illumination time	2 - 20 h
Number of rechargeable batteries contained	1
ATEX zone	no
Illumination	200 - 2000 lm
Overall height	163 mm
Overall width	63 mm
Battery capacity	4 Ah
Power supply	Rechargeable battery-powered
Overall length	163 mm
Bulb	LED module
Colour temperature	6000 K
Weight	790 g
Power consumption	16 W
Manufacturer's designation	NOVA R
Type of product	Work lamp