

Garant**Pair of gloves MASTER CUT D, Glove size: 7****Order data**

Order number	094446 7
GTIN	4062406273408
Item class	01H

Description**Version:**

Close-fitting and extremely comfortable thanks to 18-gauge knitting technology. Pleasant nitrile micro-foam coating for exceptionally good sense of touch and high degree of dexterity.

GARANT MASTER CUT D. Cut protection level D, **completely without glass or steel fibres.**

With reinforced thumb joint for increased working life.

The gloves can be washed between 40° – 60°C up to 4 times.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Series	MASTER CUT
Glove characteristics	Reinforced crook of the thumb
Knitted technology	18G
Clothing standard	Oeko-Tex Standard 100

EN 388	4442D
Backing material	Special yarn
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Application range	Precision
Colour	grey / black
Application	reusable
Cut protection class	D
Type of product	Cut-resistant gloves