

Garant**GARANT Master Mute cutting head, left-hand, System / insert size: DM/43****Order data**

Order number	264839 DM/43
GTIN	4251414902879
Item class	29D

Description**Suitable for:**

Boring bar shanks No. 264930, 264934 and 264938.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: DM

Cutting point / joint: 40 mm

ISO code cutting head: DTUNL

suitable indexable insert: TN.. 1604..

Approach angle: 93 °

Minimum pre-drill Ø D_{min}: 48 mm

Centre offset L₃: 27 mm

Technical description

Cutting point / joint	40 mm
System	DM

Shim screw	259027 1
Shim	259033 4
Series	Master Mute
Minimum pre-drill $\varnothing D_{\min}$	48 mm
Centre offset L_3	27 mm
Approach angle	93 °
Clamp, screw, O-ring	259036 6
suitable indexable insert	TN.. 1604..
ISO code cutting head	DTUNL
Overall length L	35 mm
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Clamp unit	259508
Clamp unit Type 6	259036 6
Shim screw	259611
Shim Type 4	259033 4
Shim	259226
Shim screw Type 1	259027 1