

uvex**Pair of gloves uvex phynomic airLite B ESD, Glove size: 8**

Order data

Order number	094466 8
GTIN	4048612063736
Item class	04W

Description

Version:

uvex phynomic airLite series. Particularly light-weight cut-resistant gloves with **ergonomic fit** and high wearing comfort. Ideal for activities for which high **dexterity and a good sense of touch** are required. They can be used both in ESD areas and in explosion hazard areas. Dermatologically tested (proDERM®) and free from all accelerators. The **Aqua-Polymer airLite coating** ensures high breathability.

Standard:

EN 388; EN ISO 21420

EN 16350

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. Gloves which protect against electrostatic discharges do not insulate the hands against electrical voltages. Not suitable for working on live cables or for protection against electric shock - they protect only the product.

Technical description

Type of glove	Cut-resistant gloves
---------------	----------------------

Glove size	8
Protection category	Category II
Glove characteristics	Suitable for touch screens
Knitted technology	18G
electrostatic characteristic	EGB/ESD
Clothing standard	Oeko-Tex Standard 100
EN 388	3X32B
Backing material	Dyneema®Diamond, polyamide, elastane, carbon
Coating	Nitrile
Coating variant	The palms of the hands
Application range	Precision
Colour	blue / anthracite
Weight	45 g
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves