

Garant**ZCMX 060204, Grade: HBZ030**

Order data

Order number	268423 HBZ030
GTIN	4062406273804
Item class	21E

Description

Version:

Harder substrate for longer tool life with thinner CVD coating. Especially for facing and longitudinal turning applications.

Technical description

Main application	P
Number of changes/inserts	2
Coating	CVD
Corner radius	0.4 mm
Tool material	Carbide
Cutting depth a_p	0.4 - 2 mm
Cutting conditions	continuous
ISO code indexable insert	ZCMX 060204
Grade	HBZ030

Cutting speed v_c main application	70 - 200 m/min
Feed rate f when drilling	0.03 - 0.12 mm
Feed rate f when turning	0.1 - 0.3 mm
suitable for tool dia. D_c	12 mm
Type of product	Indexable insert for turning