



Cordless impact wrench / impact driver, Type: M12FQID



Order data

Order number	074014 M12FQID
GTIN	4058546229184
Item class	03L

Description

Version:

- Robust and powerful FUEL™ cordless impact screwdriver with brushless POWERSTATE™ EC motor.
- Long motor service life and high energy efficiency.
- Sturdy metal gearbox casing and ergonomic central handle with soft-grip coating.
- Battery charge display.
- LED illumination of the working area.
- Reversible, with electronic speed control.
- REDLINK PLUS™ electronics – for unique power management.
- DRIVE CONTROL™ permits quick switching between the available settings with different speeds and torques.

When performing fastening work in wood, the M12 FUEL-DRIVE™ SURGE™ (at 76 dB(A)) the cordless impact driver is the quietest impact driver in the M12™ range.

Advantage:

DRIVE CONTROL™ .

Supplied with:

Supplied with 2x Li-ion high-power batteries, charger, HD box.

Technical description

Battery voltage	12 V
maximum vibration to EN	1.5 m/s ²
Manufacturer's designation	M12FQID-202X
Tool arbor size	1/4 in
Packaging	Modular case (HD=Heavy Duty)
maximum torque 1st step	50 Nm
maximum screw Ø (8.8 - 12.9)	M14
Number of impacts 1st stage	0 - 950 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Type of rechargeable battery	Lithium-ion
Number of impacts 3rd stage	0 - 3400 min ⁻¹
Number of impacts 2nd stage	0 - 2200 min ⁻¹
typical application	Strong
Tool arbor drive profile	HEX (E 6.3)
Weight	1.1 kg
Number of rechargeable batteries contained	2
Battery capacity	2 Ah
Power supply	Rechargeable battery-powered
Suitable for material	Steel
Type of product	Impact wrench

Accessories

Li-ion system M12B4 Battery type MB12	073815 MB12
---------------------------------------	-------------