

**3M****769F abrasive flap disc, glass fibre pad flat, Ø 125 mm, Grit: 120**

## Order data

Order number	565511 120
GTIN	5902658113369
Item class	53F

## Description

**Version:**

Coated with **precisely formed** ceramic grit mixture for **high metal removal rate and long working life**.

**Application:**

General grinding work with high-power angle grinders.

## Technical description

Grit	120
Bore Ø	22.23 mm
Shape description	flat
Disc Ø	125 mm
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %

Product name attribute	Ø 125 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
dry	suitable		