

Honeywell**Pair of gloves CoreShield™ 24-9518B, Glove size: 9**

Order data

| | |
|--------------|----------------|
| Order number | 094522 9 |
| GTIN | 13603835667130 |
| Item class | 09A |

Description

Version:

Honeywell CoreShield™ series. The innovative light-weight cut-resistant gloves series offers **very good touch sensitivity** and pleasant freedom of movement for the fingers. In addition the series scores well for long shelf life and high sturdiness. The resilient and **breathable micro-foam coating** ensures excellent non-slip characteristics for the gloves on both oily and dry surfaces.

CoreShield™ 24-9518B. Cut-resistant gloves with cut protection level D and **18-gauge knitted technology** for precision work with high cut hazards. High wearing comfort, thanks to the **HPPE-stainless steel fibre** backing material.

Standard:

EN 388; EN 420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof. The **CoreShield™ series** is available in various knitted thicknesses (10 to **18 gauge**) and coatings (nitrile micro-foam, super thin nitrile).

Colour: black

Technical description

| | |
|----------------------------|--------------------------------|
| Manufacturer's designation | CoreShield 24-9518B |
| Contents | 10 |
| Glove characteristics | Reinforced crook of the thumb |
| Glove characteristics | Suitable for touch screens |
| Glove characteristics | Silicone-free |
| Glove characteristics | Suitable for allergy sufferers |
| Glove characteristics | DMF-free |
| Knitted technology | 18G |
| Clothing standard | Oeko-Tex Standard 100 |
| EN 388:2016 | 4X31D |
| Backing material | HPPE-stainless steel |
| Coating | Nitrile micro-foam |
| Coating variant | The palms of the hands |
| Application range | All-round |
| Colour | black |
| Weight | 42-63 g |
| Length | 220 - 270 mm |
| Application | reusable |
| Cut protection class | D |
| Type of product | Cut-resistant gloves |