

Garant
GARANT Master Alu SlotMachine solid carbide roughing end mill with through-coolant HPC, DLC, Ø e8 DC: 6mm

Order data

Order number	205256 6
GTIN	4062406276942
Item class	11X

Description
Version:

For roughing.

Special profile for machining non-ferrous metals.

Improved chip evacuation due to central through-coolant. Due to the patented geometry also suitable for boring.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Up to $2 \times D$ into solid material at very high feed rates and smooth cutting action.

Ramping capability up to 45° .

Very high feed rates when plunging vertically, thanks to **special plunging geometry**.

Technical description

Shank	DIN 6535 HB to h6
Overhang length L_1 incl. recess	19 mm
Direction of infeed	horizontal, oblique and vertical
Tolerance nominal \varnothing	e8
Flute length L_c	13 mm
Overall length L	57 mm
Cutting edge $\varnothing D_c$	6 mm
Recess $\varnothing D_1$	5.5 mm

No. of teeth Z	3
Shank $\varnothing D_s$	6 mm
Feed f_z for side milling in short-chipping aluminium	0.1 mm
Feed f_z for slot milling in short-chipping aluminium	0.08 mm
Helix angle	35 degrees
Balance quality with shank	G 2.5 with HB
Corner rounding r_v	0.2 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	WR
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	yes
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	450 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	380 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N

wet maximum	suitable
Air	suitable
Services	

Shank grinding Type HB	129100 HB
------------------------	-----------