



LED work lamp, Type: 5



Order data

Order number	081415 5
GTIN	4260131238574
Item class	08C

Description

Version:

Powerful, dimmable, long-lived and robust work lamps with **flexible neck** and **sturdy magnetic base**. For connection to a 24 V mains adapter or 24 V machine control system. High-performance LED in an aluminium casing, cold white approx. 5500 Kelvin.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 250-V power supply unit.

Note:

Suitable table clamps and magnetic holders can be found under 081418/081419.

Technical description

Overall height	600 mm
Bulb	LED
Weight	800 g

Colour temperature	5500 K
Illumination	450 lm
Type of fastening	Magnetic Base
Magnetic base Ø	66 mm
Nominal voltage	250 V
ATEX zone	no
Power supply	Mains operated
IP Index of Protection	IP 65
Light output	4.5 W
Light colour	cold white
Lamp head Ø	60 mm
Type of product	Desk lamp / workstation lamp