

Garant GRIDLINE

**Auxiliary cabinet with sliding doors without raised edge, 26×20G, Height: 800mm****Order data**

Order number	932128 800
GTIN	4062406277079
Item class	9GK

**Description****Version:**

Tool auxiliary cabinet 60×28G. With sliding doors, can be locked centrally with a cylinder lock. Drawer runner mountings 26×20G and pull-out shelf runner mountings 26×20G at 25 mm intervals on both sides. **No anti-tilt device.**

**Optional extras:**

Suitable drawers are listed under No. 930633 and No. 930635, suitable pull-out shelves are listed under No. 930654 and No. 930656.

**Colour:**

Body RAL 7035 light grey, sliding doors RAL 7016 anthracite **powder-coated.**

**Note:**

Base no. 958080 – 958086 is NOT suitable.

**Technical description**

Weight	68 kg
Depth	700 mm
Drawer usable area in G	26×20
Usable height	675 mm
Width	1500 mm

Height	800 mm
Depth in G	28
Width in G	60
Material thickness	1.2 mm
Height adjustment interval	25 mm
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	26×20G
Type of product	Machine auxiliary cabinet

---

## Accessories

Slide handle for GridLine Type HU12	914226 HU12
-------------------------------------	-------------