

Garant

GARANT Master Steel solid carbide torus cutter HPC, TiAlN, Ø e8 DC / R1: 16/1,0mm



Order data

Order number	206335 16/1,0
GTIN	4062406276904
Item class	11X

Description

Version:

HPC milling cutter with **newly developed high-performance coating**. For **outstanding tool life** and **optimum metal removal rates** in a range of materials.

With **double relief ground side clearance angle**.

Tolerance: Corner radius R_1

Radius size 0.1 mm – 1 mm: $R_1 = \pm 0.003$ mm.

Radius size > 1.0 mm: $R_1 = \pm 0.005$ mm.

Application:

Especially for **high speed machining** in **mould and tool making** for **copy milling**. Excellent results for **dry milling**.

Note:

Successor product to No. 206300.

Technical description

Feed f_z for copy milling in steel < 1100 N/mm ²	0.07 mm
Overall length L	150 mm
Overhang length L_1 incl. recess	92 mm
Cutting edge $\varnothing D_c$	16 mm
Shank	DIN 6535 HA to h6
No. of teeth Z	6
Feed f_z for side milling in steel < 1100 N/mm ²	0.06 mm

Corner radius R_1	1 mm
Shank $\varnothing D_s$	16 mm
Helix angle	30 degrees
Flute length L_c	16 mm
maximum shank recess dia. D_6	15.8 mm
minimum shank recess dia. D_5	15 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	e8
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 0,2×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	180 m/min	P
Steel < 750 N/mm ²	suitable	150 m/min	P
Steel < 900 N/mm ²	suitable	110 m/min	P
Steel < 1100 N/mm ²	suitable	75 m/min	P
Steel < 1400 N/mm ²	suitable	65 m/min	P
Steel < 55 HRC	suitable	35 m/min	H

INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	80 m/min	M
GG(G)	suitable	100 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		
Services			

Shank grinding Type HB

129100 HB