



Electronic torque analyser „TruCheck™ 2“, maximum torque: 30N·m



Order data

Order number	654471 30
GTIN	5060207566667
Item class	66D

Description

Version:

- Compact, handy torque analyser.
- Screw attachment to a flat surface (table, wall etc.).
- LCD display. LED background lighting ensures good legibility under poor lighting conditions.
- The integral micro-USB 2.0 port provides the power supply.
- Units of measure: Nm.

Advantage:

- Very easy to use (reduces errors).
- Suitable even for users who are not “Calibration Specialists”.
- Only a single push button to zero the display.

Application:

Setting and testing triggering, indicating and right-hand triggering torque wrenches.

Accuracy:

Percentage measured value error $\pm 1\%$.

Supplied with:

USB power supply unit (EU/UK/US/AUS), micro USB 2.0 cable, in sturdy plastic case.

Technical description

Measuring range	1.5 - 30 Nm
Weight	1.4 kg

Torque measuring accuracy	±1 %
Display unit width	175 mm
Square drive adapter	1/4 in
Square drive adapter	3/8 in
Display unit height	64 mm
maximum torque	30 Nm
Display unit depth	72 mm
Power supply	Mains operated
Nominal voltage	100 - 240 V
External hexagon drive	10 mm
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Calibration	O4
Type of product	Torque testing device

Services

Calibration, clockwiseTorque analyser / sensor Type 400	020120 400
DAkkS calibration, clockwiseTorque analyser / sensor Type 1000	020130 1000
DAkkS calibration, clockwiseTorque analyser / sensor Type 0,1-1100	020130 0,1-1100