



## Electronic torque analyser „TruCheck™ 2 Plus“, maximum torque: 30N·m



### Order data

Order number	654476 30
GTIN	5060922236128
Item class	66D

### Description

#### Version:

- **3 user modes: Tracking display (Track) Trigger point sensing (First Peak) Peak value display (Final-Peak).**
- **Easy input of target torque with tolerances.**
- **LCD display. LED background lighting ensures good legibility under poor lighting conditions.**
- **The integral micro-USB 2.0 port provides the power supply and data transmission.**
- **12 display languages.**
- **Memory for saving up to 15 measured values.**
- **Units of measure: Nm, lbfft, lbfin.**

#### Advantage:

Quick and visually easily recognised status display thanks to change of colour of the display (red, yellow, green). Simple transmission of measured data available via a USB interface.

#### Application:

Setting and testing triggering, indicating and right-hand triggering torque wrenches. Adjusting right-hand triggering **torque screwdrivers** and **torque wrenches** with or without setting scale.

#### Accuracy:

Percentage measured value error  $\pm 1\%$ .

#### Supplied with:

USB power supply unit (EU/UK/US/AUS), micro USB 2.0 cable, in sturdy plastic case.

### Technical description

Display unit width	175 mm
Square drive adapter	1/4 in
Square drive adapter	3/8 in
Display unit depth	72 mm
Display unit height	64 mm
Torque measuring accuracy	±1 %
maximum torque	30 Nm
Measuring range	1.5 - 30 Nm
Weight	1.4 kg
Power supply	Mains operated
Nominal voltage	100 - 240 V
External hexagon drive	10 mm
Direction of tightening	Right-hand tightening
Interface	USB interface
Test certificate	Manufacturer's test certificate
Calibration	O4
Type of product	Torque testing device

## Services

Calibration, clockwiseTorque analyser / sensor Type 400	020120 400
DAkkS calibration, clockwiseTorque analyser / sensor Type 0,1-1100	020130 0,1-1100