



## Solid carbide high performance drill, Whistle-Notch shank DIN 6535 HE, TiAlN, Ø DC m7: 12,2mm



### Order data

Order number	122408 12,2
GTIN	4045197428172
Item class	12E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

### Technical description

Number of cutting edges Z	2
Flute length $L_c$	60 mm
Shank tolerance	h6
Nominal Ø $D_c$	12.2 mm
Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.15 mm/rev.
Tolerance nominal Ø	m7
Shank Ø $D_s$	14 mm
Overall length L	107 mm
Standard	DIN 6537 K
recommended maximum drilling depth $L_2$	41.7 mm
Coating	TiAlN

Tool material	Solid carbide
Version	4xD
Point angle	140 degrees
Shank	DIN 6535 HE to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	45 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	40 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	30 m/min	S
GG	suitable only under restricted conditions	70 m/min	K
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		