

**KÄRCHER****Wet and dry vacuum cleaner, Manufacturer's designation: NT22APTE****Order data**

Order number	078521 NT22APTE
GTIN	4054278287935
Item class	07C

**Description****Version:**

Powerful all-purpose **wet and dry cleaners** with high suction power and compact design, hose storage, and accessory storage on the cleaner. **Automatic shut-down** when the maximum filling level is reached in the container.

- **Folded filter enables wet and dry suction without removing the filter.**
- **The Tact automatic filter cleaning system permits uninterrupted work in combination with low maintenance costs and long working life of the filter.**
- **The central rotary switch permits easy switching between the suction programs.**

Wet / dry vacuum cleaner with device socket and automatic start-up for electric tools.

- **PES cartridge filter unaffected by moisture.**
- **Robust 22-litre container with bumpers and castors.**

**Note:**

Industrial vacuum cleaner No. 078522 for materials that are oily or contain oil.

**Technical description**

Automatic switch-on	yes
Operating noise	72 dB(A)

Cable length	6 m
Vacuum	255 mbar
Number of turbines	1
Air flow volume	71 l/s
Height	480 mm
Power consumption	1300 W
Manufacturer's designation	NT22APTE
Connection width	35 mm
Length	380 mm
Special features	Compact
Filter cleaning	ApClean semi-automatic filter cleaning
Container volume	22 l
Dust class – vacuum cleaner	L
Width	370 mm
Filter system	Cartridge filter
Weight	6.1 kg
Suction hose length	1.9 m
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

---

## Accessories

Adaptor piece, Ø 40-35 mm Connection width DN35	078538 DN35
---	-------------