


VHB™ adhesive tape, black, Width×length (mm× m): 12X33**Order data**

| | |
|--------------|---------------|
| Order number | 083789 12X33 |
| GTIN | 4001895844904 |
| Item class | 08M |

Description**Version:**

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

The **3M™ 5952** is suitable for use indoors and outdoors. It can be applied quickly and easily, and provides a high-performance and permanent bond. Use this high-performance and visco-elastic VHB adhesive tape on a wide variety of surfaces such as powder coating paint finishes.

Note:

Further 3M™ VHB™ tapes in different thicknesses and lengths are available on request. The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Technical description

| | |
|----------------------------|--------------|
| Type of adhesive tape | double-sided |
| Storage humidity | 50 % |
| Adhesive | Acrylate |
| Thickness | 1.1 mm |
| Colour | black |
| Adhesive strength on steel | 5.5 N/mm |
| "Best before" date | 12 mo |

| | |
|----------------------------|---------------------|
| Manufacturer's designation | 5952 |
| Width | 12 mm |
| Material of covering | Siliconised PE film |
| Storage temperature | 20 °C |
| Stretch capability | 300 % |
| Length | 33 m |
| Product name attribute | black |
| USP1 | VHB™ |
| USP2 | black |
| Type of product | Adhesive tape |