

**Swarf and liquid vacuum cleaner, Manufacturer's designation: VHO200****Order data**

Order number	078559 VHO200
GTIN	5711145490681
Item class	07D

**Description****Version:**

High quality, very durable Nilfisk CFM "grey line" industrial vacuum cleaner. Powerful **liquid vacuum cleaner** with high-power oil-resistant cleaning set. Equipped with **air reverse blowing valve** for simple and reliable emptying of the dirt container. A chip basket and emptying kit are already incorporated. Suitable for a very wide range of cleaning work in the metal industry.

**Supplied with:**

Supplied with chip basket, integral emptying kit including oil-resistant cleaning set.

**Note:**

Suitable accessories can be found under 078551-078552.

**Technical description**

Power consumption	2400 W
Operating noise	70 dB(A)
Vacuum	230 mbar
Container volume	75 l
Manufacturer's designation	VHO 200

Height	1230 mm
Number of turbines	1
Air flow volume	55 l/s
Width	880 mm
Weight	60 kg
Length	580 mm
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

---

## Accessories

Industrial setoil-resistant Hose Ø 50 mm	078551 50
Industrial set Hose Ø 50 mm	078552 50