


**3M****VHB™ adhesive tape, black, Width×length (mm× m): 12X33**

## Order data

Order number	083789 12X33
GTIN	4001895844904
Item class	08M

## Description

### Version:

**Double-sided** high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

The **3M™ 5952** is suitable for use indoors and outdoors. It can be applied quickly and easily, and provides a high-performance and permanent bond. Use this high-performance and visco-elastic VHB adhesive tape on a wide variety of surfaces such as powder coating paint finishes.

### Note:

Further 3M™ VHB™ tapes in different thicknesses and lengths are available on request. The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

## Technical description

Type of adhesive tape	double-sided
Storage humidity	50 %
Adhesive	Acrylate
Thickness	1.1 mm
Colour	grey
Adhesive strength on steel	5.5 N/mm

"Best before" date	12 mo
Manufacturer's designation	5952
Width	12 mm
Material of covering	Siliconised PE film
Storage temperature	20 °C
Stretch capability	300 %
Length	33 m
Product name attribute	black
Type of product	Adhesive tape