

**Tap bit, vaporised, M: M4****Order data**

Order number	130990 M4
GTIN	4062406281236
Item class	12H

Description**Version:**

With 1/4 inch hexagon shank to DIN 3126 C 6.3.

Application:

Ideal for repair and assembly work in mobile situations.

Application for type of drilling: up to 1.5×D for through holes

Standard: Manufacturer's standard

Thread standard: DIN 13

Taper lead form: B

Cutting direction: right-hand

Type of threading tool: Hand tap

Thread pitch: 0.7 mm

Overall length L tap bit: 34 mm

Thread length L_c tap bit: 11 mm

Recess Ø D₁ tap bit: 3 mm

Tapping hole Ø: 3.3 mm

Technical description

Thread length L _c tap bit	11 mm
Overall length L tap bit	34 mm
Recess Ø D ₁ tap bit	3 mm
Thread standard	DIN 13
Thread pitch	0.7 mm

Tapping hole Ø	3.3 mm
Type of threading tool	Hand tap
Taper lead form	B
Standard	Manufacturer's standard
Cutting direction	right-hand
Coating	vaporised
Thread type	M
Tool material	HSS
Tolerance class	ISO 2 6H
Flank angle	60 degrees
Application for type of drilling	up to 1.5×D for through holes
Type of product	Tap

Accessories

Tap bits set with coupling shank for metric threads M3-10	130995 M3-10
---	--------------