

Garant
ER compensating floating holder Cylindrical, Type: 25-32

Order data

Order number	319780 25-32
GTIN	4062406278410
Item class	31V

Description
Version:

Compensating holder with ER collet adaption. **Adjustable radial and angular compensation.** With through coolant feed.

Application:

Optimum for compensating alignment errors between workpiece and tool, for instance when reaming or tapping (without tension / compression compensation). For use primarily on lathes, but also suitable for milling machines.

Technical description

Overhang dimension A	58 mm
Shank \varnothing d	25 mm
for ER collets	32
External \varnothing D	69 mm
Radial compensation	1.5 mm
suitable for ER size	32
Through-coolant	yes
Type of product	Collet chuck

